

## Chromatography Solutions

# Avantor® Hichrom GC phases Cross reference guide

VISIT  
VWR.COM

Many more phases  
and formats available,  
check [vwr.com](http://vwr.com)  
or email [chromsupport@  
avantorsciences.com](mailto:chromsupport@avantorsciences.com)

AVANTOR® HICHROM GC PHASES	AGILENT / VARIAN	ALLTECH	MACHERY-NAGEL	PHENOMENEX	QUADREX	RESTEK	SGE	SUPELCO	USP METHOD CLASSIFICATION
HI-1	DB-1, HP-1, CP-Sil 5 CB	AT-1(+), EC-1(+)	OPTIMA-1	ZB-1	007-1	Rtx-1	BP1	SPB-1, Equity-1	G1, G2, G9
HI-5	DB-5, HP-5, CP-Sil 8 CB	AT-5(+), EC-5(+)	OPTIMA-5	ZB-5	007-5	Rtx-5	BP5	SPB-5, Equity-5	G27, G36
HI-1701	DB-1701, HP-1701, DB-1701P, CP-Sil 19 CB	AT-1701(+)	OPTIMA-1701	ZB-1701	007-1701	Rtx-1701	BP10	SPB-1701, Equity-1701	G46
HI-17	DB-17, HP-17, DB-608, CP-Sil 24 CB	AT-50(+)	OPTIMA-17	ZB-50	007-17	Rtx-50	BPX50	SPB-50	G3
HI-624	DB-624, HP-624	AT-624(+)	OPTIMA-1301, OPTIMA-624	ZB-624	007-624, 007-1301	Rtx-1301, Rtx-624	BP624	SPB-624	G43
HI-WAX	DB-Wax, HP-Wax, CP Wax 52 CB	AT-Wax(+), EC-Wax(+)	OPTIMA-WAX	ZB-Wax	007-CW	Rtx-Wax	BP20	-	G14, G15, G16
HI-ACID (FFAP)	DB-FFAP	AT-1000(+), EC-1000(+)	-	ZB-FFAP	007-FFAP	Stabilwax-DA	BP21	Nukol	G14, G15, G16, G25, G35, G39
HI-1 MS	DB-1 ms (UI), HP-1 ms, VF-1 ms	AT-1 ms(+)	OPTIMA-1 MS (accent)	ZB-1 ms	007-1 ms	Rxi-1 MS	BP1	Equity-1	G1, G2, G9, G38
HI-5 MS	DB-5 ms (UI), HP-5 ms	AT-5 ms(+)	OPTIMA-5 MS (accent)	ZB-5 ms	007-5 ms	Rtx-5 MS, Rxi-5 MS	BPX5	Equity-5	G27, G36, G41
HI-5 MS Xil	DB-5 ms (UI), VF-5 ms	-	OPTIMA-5 MS (accent)	ZB-5 ms	-	Rxi-5 Sil MS	-	SLB-5 ms	G27, G36, G41
HI-XMLB	DB-XLB	-	OPTIMA-XLB	ZB-XLB (HT)	-	Rtx-XLB	-	MDN-12	-
HI-35 MS	DB-35 ms (UI), VF-35 ms	-	OPTIMA-35 MS	-	007-35 ms	Rxi-35 Sil MS	BPX35	SPB-35	G28, G32, G42
HI-17 MS	DB-17 ms, VF-17 ms	-	OPTIMA-17 MS	-	-	Rxi-17 Sil MS	BPX50	-	G3
HI-624 MS	VF-1301 ms, VF-624 ms	-	OPTIMA-624 LB	-	-	Rxi-624 Sil MS	-	-	G43
HI-WAX MS	InnoWax, VF-Wax ms	AT-Wax ms(+)	-	ZB-Wax plus	-	Stabilwax MS	-	-	G14, G15, G16
HI-10	HP-88, CP-Sil 88	AT-Silar 10(+)	-	ZB-FAME	-	Rtx-2560	BPX70	SP-2560	G5, G8, G48
HI-200	DB-200, DB-210, VF-200 ms	AT-210(+)	OPTIMA-210	-	007-210	Rtx-200	-	-	G6
HI-225	DB-225, HP-225	AT-225(+)	OPTIMA-225	-	007-225	Rtx-225	BP225	SPB-225	G7, G19, G26
HI-35	DB-35, HP-35	AT-35(+)	-	ZB-35	007-11, 007-35	Rtx-35	-	SPB-35, SPB-608	G28, G32, G42
HI-50	DB-23, VF-23 ms	AT-Silar 90(+)	-	-	-	Rtx-2330	BPX70	SP-2330, SP2331, SP2380	G8
HI-FFAP EXT	DB-FFAP	AT-1000(+), EC-1000(+)	-	ZB-FFAP	007-FFAP	Stabilwax-DA	BP21	Nukol	G14, G15, G16, G25, G35, G39

This is a general phase-to-phase cross reference which holds for the vast majority of GC applications. It is possible that owing to differences in manufacturing process small differences in selectivity could occur.

[vwr.com/avantorcolumns](http://vwr.com/avantorcolumns)

## About VWR, part of Avantor

As Avantor's channel brand, VWR serves as a leading global provider of product and service solutions to laboratory and production customers in the pharmaceutical, biotechnology, industrial, education, government and healthcare industries, and offers an integrated, seamless purchasing experience that is optimized for the way our customers do business. We set science in motion to create a better world. For more information, visit [avantorsciences.com](http://avantorsciences.com) or [vwr.com](http://vwr.com).



### AUSTRIA

VWR International GmbH  
Graumanngasse 7  
1150 Vienna  
Tel.: +43 1 97 002 0  
[info.at@vwr.com](mailto:info.at@vwr.com)

### BELGIUM

VWR International bv  
Researchpark Haasrode 2020  
Geldenaaksebaan 464  
3001 Leuven  
Tel.: +32 (0) 16 385 011  
[vwr.be@vwr.com](mailto:vwr.be@vwr.com)

### CANADA

VWR International  
2360 Argentia Road  
Mississauga, Ontario L5N 5Z7  
Tel.: +1 800 932 5000  
[Canada\\_Orders@vwr.com](mailto:Canada_Orders@vwr.com)

### CHINA

VWR (Shanghai) Co., Ltd  
Bld.No.1, No.3728 Jinke Rd,  
Pudong New District  
Shanghai, 201203- China  
Tel.: 400 821 8006  
[info\\_china@vwr.com](mailto:info_china@vwr.com)

### CZECH REPUBLIC

VWR International s. r. o.  
Veetee Business Park  
Pražská 442  
CZ - 281 67 Stříbrná Skalce  
Tel.: +420 321 570 321  
[info.cz@vwr.com](mailto:info.cz@vwr.com)

### DENMARK

VWR International A/S  
Tobaksvejen 21  
2860 Søborg  
Tel.: +45 43 86 87 88  
[info.dk@vwr.com](mailto:info.dk@vwr.com)

### FINLAND

VWR International Oy  
Valimotie 9  
00380 Helsinki  
Tel.: +358 (0) 9 80 45 51  
[info.fi@vwr.com](mailto:info.fi@vwr.com)

### FRANCE

VWR International S.A.S.  
Le Périgores – Bâtiment B  
201, rue Carnot  
94126 Fontenay-sous-Bois cedex  
Tel.: 0 825 02 30 30\* (national)  
Tel.: +33 (0) 1 45 14 85 00 (international)  
[info.fr@vwr.com](mailto:info.fr@vwr.com)  
\* 0,18 € TTC/min + prix appel

### GERMANY

VWR International GmbH  
Hilpertstraße 20a  
D - 64295 Darmstadt  
Tel.: 0800 702 00 07\* (national)  
Tel.: +49 (0) 6151 3972 0 (international)  
[info.de@vwr.com](mailto:info.de@vwr.com)  
\*Freecall

### HUNGARY

VWR International Kft.  
Simon László u. 4.  
4034 Debrecen  
Tel.: +36 52 521130  
[info.hu@vwr.com](mailto:info.hu@vwr.com)

### INDIA

Avantor Performance Materials India Limited  
17th Floor, Building No. 5, Tower C  
DLF Cyber City Phase – III  
Gurgaon - 122002, Haryana  
Tel.: +91-1244-65-6700  
[chromatography.india@avantorsciences.com](mailto:chromatography.india@avantorsciences.com)

### IRELAND

VWR International Ltd  
Orion Business Campus  
Northwest Business Park  
Ballycoolin  
Dublin 15  
Tel.: +353 (0) 1 88 22 222  
[sales.ie@vwr.com](mailto:sales.ie@vwr.com)

### ITALY

VWR International S.r.l.  
Via San Giusto 85  
20153 Milano (MI)  
Tel.: +39 02 3320311  
[info.it@vwr.com](mailto:info.it@vwr.com)

### KOREA

VWR International ~  
17, Daehak 4-ro, Yeongtong-gu,  
Suwon-si, Gyeonggi-do  
Tel.: +82 31 645 7256  
[saleskorea@avantorsciences.com](mailto:saleskorea@avantorsciences.com)

### THE NETHERLANDS

VWR International B.V.  
Postbus 8198  
1005 AD Amsterdam  
Tel.: +31 (0) 20 4808 400  
[info.nl@vwr.com](mailto:info.nl@vwr.com)

### MEXICO

VWR International, S.de R.L. de C.V.  
Km. 14.5 Carretera  
Tlalnepantla-Cuautitlán  
Col. Lechería  
Tultitlán Edo. de México  
CP 54940  
Tel.: +52 (55) 5005 0100  
[vwrmx@vwr.com](mailto:vwrmx@vwr.com)

### MIDDLE EAST & AFRICA

VWR International FZ-LLC  
Office 203, DSP Lab Complex,  
Dubai Science Park,  
Dubai, United Arab Emirates  
Tel.: +971 4 5573271  
[Info.mea@vwr.com](mailto:Info.mea@vwr.com)

### NORWAY

VWR International AS  
Brynsalleen 4,  
0667 Oslo  
Tel.: +47 22 90 00 00  
[info.no@vwr.com](mailto:info.no@vwr.com)

### POLAND

VWR International Sp. z o.o.  
Limbowa 5  
80-175 Gdansk  
Tel.: +48 58 32 38 200  
[info.pl@vwr.com](mailto:info.pl@vwr.com)

### PORTUGAL

VWR International -  
Material de Laboratório, Lda  
Centro Empresarial de Alfragide  
Rua da Indústria, nº 6  
2610-088 Amadora  
Tel.: +351 21 3600 770  
[info.pt@vwr.com](mailto:info.pt@vwr.com)

### SINGAPORE

VWR Singapore Pte Ltd  
18 Gul Drive  
Singapore 629468  
Tel.: +65 6505 0760  
[sales.sg@vwr.com](mailto:sales.sg@vwr.com)

### SPAIN

VWR International Eurolab S.L.U.  
C/ Tecnología 5-17  
A-7 Llinars Park  
08450 - Llinars del Vallès  
Barcelona  
Tel.: +34 902 222 897  
[info.es@vwr.com](mailto:info.es@vwr.com)

### SWEDEN

VWR International AB  
Fagerstagatan 18a  
163 94 Stockholm  
Tel.: +46 (0) 8 621 34 00  
[kundservice.se@vwr.com](mailto:kundservice.se@vwr.com)

### SWITZERLAND

VWR International GmbH  
Lerzenstrasse 16/18  
8953 Dietikon  
Tel.: +41 (0) 44 745 13 13  
[info.ch@vwr.com](mailto:info.ch@vwr.com)

### UK

VWR International Ltd  
Customer Service Centre  
Hunter Boulevard - Magna Park  
Lutterworth  
Leicestershire  
LE17 4XN  
Tel.: +44 (0) 800 22 33 44  
[uksales@vwr.com](mailto:uksales@vwr.com)

### UNITED STATES

VWR International, LLC  
100 Matsonford Road  
Building One Suite 200  
Radnor, PA 19087  
Tel.: +1 800 932 5000  
[VWRCustomerService@vwr.com](mailto:VWRCustomerService@vwr.com)

## GO TO [VWR.COM](http://VWR.COM) FOR THE LATEST NEWS, SPECIAL OFFERS AND DETAILS FROM YOUR LOCAL VWR SUPPORT TEAM

Prices, product, and/or services details are current when published and subject to change without notice. | Certain products or services may be limited by country, federal, state, provincial, or local regulations. | VWR, part of Avantor, makes no claims or warranties concerning sustainable/green products. Any claims concerning sustainable/green products are the sole claims of the manufacturer and not those of VWR International, LLC and/or Avantor, Inc. or affiliates. Offers valid in countries listed above, void where prohibited by law or company policy, while supplies last. | Trademarks are owned by Avantor, Inc. or its affiliates, unless otherwise noted. | Visit [vwr.com](http://vwr.com) to view our privacy policy, trademark owners, and additional disclaimers.